

# Specifications

## Eaton BR3060LQN200RG



Eaton BR main lug loadcenter, 200 A,D1R,Aluminum, NEMA 1,Metallic,10 kAIC,Combination,NEMA 1,60 Circuits,Twenty-four pole,30 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#1 AWG-300 kcmil Cu/Al

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BR3060LQN200RG
<b>UPC</b>	786676026321
<b>PRODUCT LENGTH/DEPTH</b>	5.19 in
<b>PRODUCT HEIGHT</b>	29.13 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	35 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 50 UL 67
<b>CATALOG NOTES</b>	GBK2120 installed

## Product specifications

TYPE	Main lug
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MOUNTING	Combination
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	D1R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BR3060LQN200RG](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton BR3060LQN200RG



Eaton BR main lug loadcenter, 200 A,D1R,Aluminum, NEMA 1,Metallic,10 kAIC,Combination,NEMA 1,60 Circuits,Twenty-four pole,30 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#1 AWG-300 kcmil Cu/Al

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BR3060LQN200RG
<b>UPC</b>	786676026321
<b>PRODUCT LENGTH/DEPTH</b>	5.19 in
<b>PRODUCT HEIGHT</b>	29.13 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	35 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 50 UL 67
<b>CATALOG NOTES</b>	GBK2120 installed

## Product specifications

TYPE	Main lug
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MOUNTING	Combination
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	D1R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BR3060LQN200RG](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

