



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR345 BR 3P 45A 10KAIC BKR

Eaton Corp

Catalog Number	BR345
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 45 A, 10 Kaic, Three-Pole, 240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	0.9400 (lbs/each)
Product Category	3 Pole Standard Trip Plug-In

Features

dimensions	3.0000 IN X 3.0000 IN X 2.7500 IN
interrupt rating	10 kAIC
Poles	3
Trip Type	Common breaker trip
Voltage Rating	240 V - 240 V

Descriptions

Description	BR 3P 45A 10KAIC BKR
extra long description	ETN BR345 BR 3P 45A 10KAIC BKR
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 45 A, 10 kAIC, Three-pole, 240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	BR 3P 45A 10KAIC BKR
Special Features	Used with Type BR Loadcenters

Manufacturer Information

Brand	Eaton
GTIN	00786676000116
Manufacturers Part Number	BR345
UPC	786676000116

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.94

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Generation - Conventional Energy - Conventional Energy Datacenters - IT Space: CI and Hyper Converged Marine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489, Federal Specifications Classification W-C375