

Specifications



Eaton BRP16N200

Eaton BR convertible
loadcenter, Convertible, 200
A, X4, Aluminum, Cover included, NEMA
1, Metallic, 10 kAIC, CSR, Combination, 32
Circuits, Single-pole, 16 Spaces, Two hots, a
neutral, and a ground, Single-phase, Type BR
1-inch breakers, 120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP16N200
UPC	786689053147
PRODUCT LENGTH/DEPTH	27 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26.8 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
PRODUCT TYPE	Convertible loadcenter



Powering Business Worldwide

Product specifications

TYPE	Convertible
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
MOUNTING	Combination
NUMBER OF CIRCUITS	32
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	16
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X4
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	Two hots, neutral and ground

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP16N200
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

