

Specifications

Eaton BRP20L150

Eaton Eaton BR main lug loadcenter, Main lug only, 150 A, X3, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2125, NEMA1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #1-300 kcmil

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP20L150
UPC	786689053246
PRODUCT LENGTH/DEPTH	23 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	21 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67

Product specifications		Resources	
TYPE	MLO	SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP20L150
AMPERAGE RATING	150 A		
BUS MATERIAL	Aluminum	WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024
COVER	Cover included		
MAIN CIRCUIT BREAKER	CSR2125		
NUMBER OF CIRCUITS	40		
NUMBER OF POLES	Single-pole		
NUMBER OF SPACES	20		
PHASE	Single-phase		
USED WITH	Type BR 1-inch breakers		
VOLTAGE RATING	120/240V		
BOX SIZE	X3		
ENCLOSURE	NEMA 1		
ENCLOSURE MATERIAL	Metallic		
INTERRUPT RATING	10 kAIC		
NEMA RATING	NEMA 1		
NUMBER OF WIRES	Two hots, neutral and ground		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

