

Specifications

Eaton BRP30BC100

Eaton BR main breaker
loadcenter, 100A, X5, Copper, Cover
included, NEMA 1, Metallic, 10kAIC, BR2100, 60
circuits, Single pole, 30 spaces, Two hots, a
neutral, and a ground, Single-
phase, Combination, Type BR 1-inch
breakers, 120/240V

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BRP30BC100
UPC	786689052829
PRODUCT LENGTH/DEPTH	29 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	27.5 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications

TYPE	Plug-on neutral main circuit breaker loadcenter
AMPERAGE RATING	100 A
BUS MATERIAL	Copper
COVER	Cover included
MAIN CIRCUIT BREAKER	BR2100
NUMBER OF CIRCUITS	60
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	30
PHASE	Single-phase
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X5
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	Two hots, neutral and ground

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP30BC100](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

