

# Specifications



# Eaton BRP30L200GW

Eaton Eaton BR main lug loadcenter, Indoor, Main lug only, 200 A, X5, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2200, Surface, flush, NEMA 1, 60 Circuits, Twenty-four pole, 30 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V, #1–300 kcmil

## General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BRP30L200GW
<b>UPC</b>	786689052904
<b>PRODUCT LENGTH/DEPTH</b>	29.12 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	26.3 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 67 UL 50

## Product specifications

<b>TYPE</b>	MLO
<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	CSR2200
<b>MOUNTING</b>	Surface, flush
<b>NUMBER OF CIRCUITS</b>	60
<b>NUMBER OF POLES</b>	Single-pole
<b>NUMBER OF SPACES</b>	30
<b>PHASE</b>	Single-phase
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240V
<b>BOX SIZE</b>	X5
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	10 kAIC
<b>NEMA RATING</b>	NEMA 1
<b>NUMBER OF WIRES</b>	Two hots, neutral and ground

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP30L200GW](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

