# Specifications



### Photo is representative





## Eaton BRP40N200RG

Eaton BR convertible loadcenter, Ground bar, Converible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Singlepole, 40 Spaces, Three-wire, Singlephase, Type BR 1-inch breakers, 120/240 V

General specifications	
PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP40N200RG
UPC	786689059064
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.13 in
PRODUCT WEIGHT	27 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Product specification	IS
SPECIAL FEATURES	Ground bar
ТҮРЕ	Converible
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
MOUNTING	Combination
NUMBER OF CIRCUITS	80
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	40
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X8
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP40N200RG
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

information.





Follow us on social media to get the

latest product and support





# Specifications



### Photo is representative





## Eaton BRP40N200RG

Eaton BR convertible loadcenter, Ground bar, Converible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Singlepole, 40 Spaces, Three-wire, Singlephase, Type BR 1-inch breakers, 120/240 V

General specifications	
PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP40N200RG
UPC	786689059064
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.13 in
PRODUCT WEIGHT	27 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Product specification	IS
SPECIAL FEATURES	Ground bar
ТҮРЕ	Converible
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
MOUNTING	Combination
NUMBER OF CIRCUITS	80
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	40
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X8
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP40N200RG
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

information.





Follow us on social media to get the

latest product and support



