

# Eaton BRSUR3040N200

Catalog Number: BRSUR3040N200

Eaton BR surge loadcenter, Factory integrated surge, Convertible main, 200 A, L1, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 30/40 Circuits, 30 Spaces, Three-wire, Single-phase, 120/240 V



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR surge loadcenter	BRSUR3040N200
<b>UPC</b>	<b>Product Length/Depth</b>
782116417124	3.88 in
<b>Product Height</b>	<b>Product Width</b>
39 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
39 lb	10 year

## Certifications

UL 67  
UL 50

## Product specifications

### Special features

Factory integrated surge

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Mounting

Combination

### Number of circuits

40

### Number of spaces

30

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

L1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

Eaton Specification Sheet - BRSUR3040N200

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)