



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



**BT1.5IM Cable Tie**  
*Panduit Corporation*

Catalog Number	BT1.5IM
Manufacturer	Panduit Corporation
Description	The BT1.5I-M Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless-Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Intermediate Cross Section, 6.1" (155MM) Length. Appropriate For Indoor Use, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 1000.
Weight per unit	1.5 (lbs/each)
Product Category	Cable Ties & Wraps

## Features

media	Yes
Tensile Strength	40

## Dimensions and Weight

Length	6.1
Thickness	0.04

## Descriptions

Description	CABLE TIE
extra long description	PAN BT1.5I-M Dome-Top® BT1.5I-M Bar
Long Description	The BT1.5I-M Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Intermediate cross section, 6.1" (155mm) length. Appropriate for Indoor use, made of Nylon 6.6, are natural in color and come in packages of 1000.
Product Type	Dome-Top® BT1.5I-M Barb Tie, PA6.6, 6.1"L, 40LB, PK1000
Special Features	Indoor

## Manufacturer Information

Brand	PANDUIT
GTIN	00074983413454
Manufacturers Part Number	BT1.5I-M
UPC	074983413454



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

## Packaging

Carton	1000
Package	5000
Weight Per each	1.51

## Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, OPL-AS23190, CSA Certified, RoHS Compliant
----------	---