

# Eaton C0300E5E

Catalog Number: C0300E5E

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 300 va , cu magnet wire

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type MTE industrial control transformer	C0300E5E
	<b>UPC</b>
	786680420429
<b>Product Length/Depth</b>	<b>Product Height</b>
5.118 in	4.764 in
<b>Product Width</b>	<b>Product Weight</b>
5.236 in	15.5 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	CSA Certified
	UL Listed
	cUL Certified

## Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

## Physical Attributes

### Coil material

Copper windings

### Design

MTE

### Tap size

None

## Performance Ratings

### Primary voltage

200/220/440 V, 208/230/460 V, 240/480 V

### Temperature rating

55°C

### Volt ampere rating

300 VA

### Secondary voltage

23/110 V, 24/115 V, 25/120 V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - C0300E5E](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)