

# Eaton C0500E6U

Catalog Number: C0500E6U

Eaton Type MTE industrial control transformer, pv:  
240/416/480/600v, 230/400/460/575v, 220/380/440/550v,  
208/500v, cu magnet wire, taps: none, sv: 99/120/130v,  
95/115/125v, 91/110/120v, 85/100/110v, 55°C, 500 va



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type MTE industrial control transformer	C0500E6U
	<b>UPC</b>
	786680019159
<b>Product Length/Depth</b>	<b>Product Height</b>
7.008 in	4.449 in
<b>Product Width</b>	<b>Product Weight</b>
5.236 in	25.6 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	CSA Certified
	cUL Certified
	UL Listed

## Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

## Physical Attributes

### Coil material

Copper windings

### Design

MTE

### Tap size

None

## Performance Ratings

### Primary voltage

208/500 V, 220/380/440/550 V, 230/400/460/575 V,  
240/416/480/600 V

### Temperature rating

55°C

### Volt ampere rating

500 VA

### Secondary voltage

99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - C0500E6U](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)