



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C1000E2A 1000 Va Type Mte Control Transformer

Eaton Corp

Catalog Number	C1000E2A
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, SV: 120/115/110V, 55°C, 1000 Va
Weight per unit	34.0 (lbs/each)
Product Category	Core & Coil Industrial Control

Features

dimensions	6.4570 IN X 6.7320 IN X 5.6690 IN
kva rating	1000 VA
Primary Voltage	220 X 440 V, 230 X 460 V, 240 X 480 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	1000 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C1000E2A 1000 VA Type MTE Contr
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 1000 va
Product Type	1000 Va Type Mte Control Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680125508
Manufacturers Part Number	C1000E2A
UPC	786680125508

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 34

Uses, Certifications, and Standards

Application Other

standard CSA Certified,cUL Certified,UL Listed,RoHS Compliant

Temperature Rating 55°C