



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C16N 16-14AWG Closed End Wire Nyl Conn W/CRMP SLV

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | C16N  |
| Manufacturer     | Nsi Industries  |
| Description      | The Easy-Twist C16-N 100-Count Pack Of Nylon Closed-End Wire Connectors Are Designed For Use On Pre-Insulated Wires In The 22-14 Awg Size Range. Theyâ€™re UL-Certified As Self-Extinguishing and Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Closed-End Nylon Connector Features An Internal Metal Crimp Sleeve That Can Be Tightened Over Twisted Pre-Insulated Wires to Form A Safe and Secure Join. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need T |
| Weight per unit  | 0.1520 (lbs/each)   |
| Product Category | Small Terminals & Connectors  |

### Features

|                |              |
|----------------|--------------|
| insulation     | Nylon 6-6    |
| Material       | Nylon        |
| Poles          | 1            |
| Voltage Rating | 300          |
| Warranty       | 1 YEAR       |
| Wire Size      | 22-14 AWG    |
| Wire Type      | CU Wire Only |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | White |
| Finish | NYLON |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 16-14AWG CLOSED END WIRE NYL CONN W/CRMP SLV  |
| extra long description | NSI C16-N CU CMP Splice Long 350 MC   |
| Features               | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These closed-end connectors feature a corrosion and chemical resistant nylon cover over a metal crimp cap wire terminal. These connectors are easy to install; simply twist your wires together to form a connection, then slide the closed end butt connector over the pigtail and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these closed-end conn |
| Long Description       | The Easy-Twist C16-N 100-Count Pack of Nylon Closed-End Wire Connectors are designed for use on pre-insulated wires in the 22-14 AWG size range. Theyâ€™re UL-certified as self-extinguishing and rated for a maximum temperature of 105Ëš Celsius (221Ëš Fahrenheit). The closed-end nylon connector features an internal metal crimp sleeve that can be tightened over twisted pre-insulated wires to form a safe and secure join. Their compact design is useful for applications in tight areas or anywhere else you need t |
| Product Type           | Cu CMP Splice Long 350 MCM  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381068019 |
| Manufacturers Part Number | C16-N          |
| sub brand                 | Easy Twist     |
| UPC                       | 662381068019   |

## Taxonomies, Classifications, and Categories

|                      |           |
|----------------------|-----------|
| Category Description | TERMINALS |
|----------------------|-----------|

## Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Weight Per each | 0.152 |

## Uses, Certifications, and Standards

|                          |       |
|--------------------------|-------|
| environmental conditions | 105 C |
| Temperature Rating       | 105 C |