




NOMINAL DUCT SIZE (W)	C in (mm)	TC in (mm)	HC in (mm)
.5	.69 (17.5)	.040 (1.0)	.230 (5.8)
.75	.94 (23.8)	.050 (1.3)	.240 (6.1)
1	1.25 (31.8)	.060 (1.5)	.350 (8.9)
1.5	1.75 (44.5)	"	"
2	2.25 (57.2)	"	"
2.5	2.75 (69.9)	"	"
3	3.25 (82.6)	.065 (1.6)	.370 (9.4)
4	4.25 (108.0)	"	"
6	6.25 (158.8)	.080 (2.0)	"

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESIS ARE METRIC.

PART NO. SYSTEM
COVER EXAMPLE
TYPE C 1.5 LG 6
WIDTH
COLOR
LENGTH (ft)

CAD FILENAME/LAYERS		D34518BA_PVC_COVER_02A	
<h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS			
WIRING DUCT COVER FOR DUCT TYPES "S", "D", "E", "F", "FS", AND "G" CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) : (.XXX) : (.XX) : ANGLES :		NONE	
2	8-24-01	JCST	JKG
D. CHANGED TOLERANCE C. MADE "C" A REFERENCE DIMENSION		34518-17	JKG
1	2/11/00	JHNU	HIW
B. .18 WAS .125/ 4.5 WAS 3.2 A. REV'D TITLE: ADDED FS AND G DUCT TYPE		34518-17	HIW
R	10-29-93	DW	CEF
RELEASED TO PRODUCTION.		34518-17	CEF
REV	DATE	BY	CHK
DESCRIPTION		ECN	R CUST SUP
DRAWN BY DW		MAT'L: POLYVINYL CHLORIDE	
DATE 10-29-93		DRAWING NO. 34518-17	
CHK'D CEF		Dwg SIZE A	



NOMINAL DUCT SIZE (W)	C in (mm)	TC in (mm)	HC in (mm)
.5	.69 (17.5)	.040 (1.0)	.230 (5.8)
.75	.94 (23.8)	.050 (1.3)	.240 (6.1)
1	1.25 (31.8)	.060 (1.5)	.350 (8.9)
1.5	1.75 (44.5)	"	"
2	2.25 (57.2)	"	"
2.5	2.75 (69.9)	"	"
3	3.25 (82.6)	.065 (1.6)	.370 (9.4)
4	4.25 (108.0)	"	"
6	6.25 (158.8)	.080 (2.0)	"

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESIS ARE METRIC.

PART NO. SYSTEM
COVER EXAMPLE
TYPE C 1.5 LG 6
WIDTH
COLOR
LENGTH (ft)

CAD FILENAME/LAYERS		D34518BA_PVC_COVER_02A	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
WIRING DUCT COVER FOR DUCT TYPES "S", "D", "E", "F", "FS", AND "G" CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) : (.XXX) : (.XX) : ANGLES :		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	8-24-01	JCST	JKG
D. CHANGED TOLERANCE C. MADE "C" A REFERENCE DIMENSION		34518-17	JKG JKG
1	2/11/00	JHNU	HIW
B. .18 WAS .125/ 4.5 WAS 3.2 A. REV'D TITLE: ADDED FS AND G DUCT TYPE		34518-17	HIW HIW
R	10-29-93	DW	CEF
RELEASED TO PRODUCTION.		34518-17	CEF
REV	DATE	BY	CHK
DESCRIPTION		ECN	R CUST SUP
DRAWN BY DW		MAT'L: POLYVINYL CHLORIDE	
DATE 10-29-93		SCALE NONE	
CHK'D CEF		DRAWING NO. 34518-17	
		DWG SIZE A	