



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C371F6 Operator Mechanism

Eaton Corp

Catalog Number	C371F6
Manufacturer	Eaton Corp
Description	Type C371 Circuit Breaker Operator Mechanism, 250A or 400A Frame, Flange Mounted, 6.5-16.63 Variable Depth Mounting Range, HMCP and Series C-HJD, JD, JDB, JDC-Frame or DK, HKD, KD, KDB-Frame, For Nema 4-4X Enclosures, With 4-Inch Handle
Weight per unit	6.0 (lbs/each)
Product Category	Circuit Breaker Accessories

Features

dimensions	16.8440 IN X 6.5630 IN X 5.0630 IN
media	Yes

Descriptions

Description	OPERATOR MECHANISM
extra long description	ETN C371F6 OPERATOR MECHANISM
Features	Eaton's Electrical Sector under the Eaton brand offers the widest variety of molded case circuit breakers available today. Designed for electrical and machinery OEMs serving a range of industries and applications these proven designs incorporate the latest in innovation with the high reliability that has been our hallmark since the advent of the circuit breaker in the 1920s
Long Description	Type C371 Circuit Breaker Operator Mechanism, 250A or 400A frame, Flange mounted, 6.5-16.63 variable depth mounting range, HMCP and Series C-HJD, JD, JDB, JDC-frame or DK, HKD, KD, KDB-frame, For NEMA 4-4X enclosures, With 4-inch handle
Product Type	Operator Mechanism

Manufacturer Information

Brand	Eaton
GTIN	00782113629841
Manufacturers Part Number	C371F6
UPC	782113629841

Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Molded case circuit breaker accessory

Packaging

Carton	1
Weight Per each	6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

UL Listed, IEC/EN 60947-4-1, IEC Rated