



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C440A1A045SF2 C440 OI 9-45A FRDM SZ 2 Standard *Eaton Corp*

Catalog Number	C440A1A045SF2
Manufacturer	Eaton Corp
Description	Eaton C440 Electronic Overload Relay, C440 Electronic Overload Relay - Nema, Freedom Size 2, 45MM Frame, Selectable 10A, Class 10 , 20, 30, Overload 9-45A, Standard
Weight per unit	0.8700 (lbs/each)
Product Category	Overload Relays & Accessories

Features

dimensions	7.5000 IN X 3.0000 IN X 6.5000 IN
Trip Type	Selectable 10 A, class 10 ,20, 30

Dimensions and Weight

Size	Freedom Size 2
------	----------------

Descriptions

Description	C440 OL 9-45A FRDM SZ 2 STANDARD
extra long description	ETN C440A1A045SF2 C440 OL (9-45A) F
Features	The C440/XTOE electronic overload relay delivers enhanced motor protection and communications capabilities in a single compact device, directly monitoring motor current in each phase. Thermal modeling is performed electronically with precision solid-state components.
Long Description	Eaton C440 electronic overload relay, C440 Electronic Overload Relay - NEMA, Freedom Size 2, 45mm frame, Selectable 10A, Class 10 ,20, 30, Overload 9-45A, Standard
Product Type	C440 OI (9-45A) FRDM SZ 2 Standard
Special Features	Standard

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685411903
Manufacturers Part Number	C440A1A045SF2
UPC	786685411903

Taxonomies, Classifications, and Categories

Type	Electronic overload relay
------	---------------------------

Packaging

Carton	1
Weight Per each	0.87



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

CSA Certified,UL Listed,CE Marked