



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3520 S Sam Houston Pkwy East Suite 900
77047-0000, TX Houston
Phone: 281-412-7049
Fax: 281-412-7314



C560M 60 Min Twist Timer With Metal Wallplate

Nsi Industries

Catalog Number	C560M
Manufacturer	Nsi Industries
Description	Twist Timer, 60 Min Time Setting Mode, SPDT;SPST Contact Form, 60 Min Time Setting, 125/250/277 V Ac, Single Gang Wall Plate Connection, Metal Brushed Aluminum, +32 °F Operating Temperature, +122 °F Operating Temperature, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	60 Minute

Descriptions

Description	60 MIN TWIST TIMER WITH METAL WALLPLATE
extra long description	TORK C560M 60 Minute Spring Wound T

Manufacturer Information

GTIN	00786261155054
UPC	786261155054

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
----------------------	-------------

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Enclosure	Single Gang Wall Plate
Frequency Rating	50-60 Hz
Operating Temperature	32-122 F