



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C8N 8AWG Closed End Wire Nyl Conn W/CRMP SLV

*Nsi Industries*

|                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | C8N                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Manufacturer     | Nsi Industries                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Description      | The Easy-Twist C8-N 40-Count Pack Of Nylon Closed-End Wire Connectors Are Designed For Use On Pre-Insulated Wires In The 16-10 Awg Size Range. Theyâ€™re UI-Certified As Self-Extinguishing and Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Closed-End Nylon Connector Features An Internal Metal Crimp Sleeve That Can Be Tightened Over Twisted Pre-Insulated Wires to Form A Safe and Secure Join. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to |
| Weight per unit  | N/A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Product Category | Small Terminals & Connectors                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |

### Features

|                      |              |
|----------------------|--------------|
| insulation           | Nylon 66     |
| Material             | Nylon        |
| Number of Conductors | 1            |
| Poles                | 1            |
| Voltage Rating       | 300 V        |
| Warranty             | 1 YEAR       |
| Wire Size            | 16-10 AWG    |
| Wire Type            | CU Wire Only |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | White |
| Finish | NYLON |

### Dimensions and Weight

|      |                          |
|------|--------------------------|
| Size | H=1.09 - W=.563 -ID=.209 |
|------|--------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 8AWG CLOSED END WIRE NYL CONN W/CRMP SLV                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| extra long description | NSI C8-N 8 Awg Closed End Connector                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Features               | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These closed-end connectors feature a corrosion and chemical resistant nylon cover over a metal crimp cap wire terminal. These connectors are easy to install; simply twist your wires together to form a connection, then slide the closed end butt connector over the pigtail and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these closed-end conn |
| Long Description       | The Easy-Twist C8-N 40-Count Pack of Nylon Closed-End Wire Connectors are designed for use on pre-insulated wires in the 16-10 AWG size range. They are UL-certified as self-extinguishing and rated for a maximum temperature of 105°C (221°F). The closed-end nylon connector features an internal metal crimp sleeve that can be tightened over twisted pre-insulated wires to form a safe and secure join. Their compact design is useful for applications in tight areas or anywhere else you need to                      |
| Product Type           | 8 Awg Closed End Connector-Nylon - 30/Pack                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Special Features       | 16-10 AWG - UL94 V-2 - Made From Nylon 66 - 40 Pcs Blister                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381362094 |
| Manufacturers Part Number | C8-N           |
| UPC                       | 662381362094   |

## Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | TERMINALS             |
| Type                 | Closed End Connectors |

## Availability

|             |    |
|-------------|----|
| minimum qty | 30 |
|-------------|----|

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 30 |
| Weight Per each | 0  |

## Uses, Certifications, and Standards

|                          |               |
|--------------------------|---------------|
| Application              | Splicing Wire |
| environmental conditions | 105 C         |
| standard                 | UL 486C       |
| Temperature Rating       | 105 C         |