



These circulators should be used in clean and dry commercial applications - such as schools, shops, offices or warehouses.

## Commercial Circulator

**Motor, blades, guards, and mount are packed and shipped in a single UPS-able carton.**



PEDESTAL MOUNT



WALL MOUNT

### Features

- Pull chain switch.
- SJT type 3 conductor, 9' long cord.
- Coated steel guards with retaining clips.
- Steel hub/spider aluminum paddle blades.
- Pole adjusts center of fan from 43" to 60".
- Meets OSHA standards.
- 1 Year limited warranty.
- Imported to TPI specifications

### Motor Specifications

- 1-Phase
- 1/4 HP, 1/3 HP on HD Models
- Ball bearing
- Open ventilated
- 120V
- 2 or 3-Speed
- Permanently lubricated
- Permanent split capacitor

### Standard Models

MFG CATALOG NUMBER	MFG MODEL NUMBER	SIZE	HP	TYPE	MOUNT TYPE	CFM*			VELOCITY PROFILE	AMPS (HIGH)	WT. (LBS)
						HIGH	MED	LOW	CFM / Area Sq Ft		
08706202	CACU 24-P	24"	1/4	Standard	Pedestal Mount	3400	3100	2800	5400 / 220	2.3	63
08706402	CACU 24-W				Wall Mount						43
08697402	CACU 30-P	30"			Pedestal Mount	4200	3800	3500	6700 / 240	2.4	66
08706302	CACU 30-W				Wall Mount						46
08761702	CACU 30-P-HD	30"	1/3	Heavy Duty	Pedestal Mount	5000	4600	4200	7000 / 250	3.60	56

\*Measured 2 feet from face of fan

Note: Stocked models may differ in appearance from photograph

# TPI Commercial Oscillating Fans

**Commercial wall mount and pedestal fans now available from TPI.**

Units imported to TPI specifications.

### Standard Models



MFG CATALOG NUMBER	MFG MODEL NUMBER	SIZE	HP	TYPE	MOUNT TYPE	CFM*			VELOCITY PROFILE	AMPS			WT. (LBS)
						HIGH	MED	LOW	CFM / Area Sq Ft	HIGH	MED	LOW	
08748902	CACU 24-PO	24"	1/4	Standard	Pedestal Mount	3200	3000	2800	5100 / 230	1.45	1.15	1.1	68
08749102	CACU 24-WO				Wall Mount								48
08749002	CACU 30-PO	30"			Pedestal Mount	4200	3800	3500	6700 / 250	2.0	1.8	1.6	70
08749202	CACU 30-WO				Wall Mount								51
08761802	CACU 30-PO-HD	30"	1/3	Heavy Duty	Pedestal Mount	5000	4600	4200	7000 / 250	3.60	3.02	2.94	64

\*Measured 2 feet from face of fan

Note: Stocked models may differ in appearance from photograph - sizes are nominal.



These circulators should be used in clean and dry commercial applications - such as schools, shops, offices or warehouses.

## Commercial Circulator

Motor, blades, guards, and mount are packed and shipped in a single UPS-able carton.



PEDESTAL MOUNT



WALL MOUNT

### Features

- Pull chain switch.
- SJT type 3 conductor, 9' long cord.
- Coated steel guards with retaining clips.
- Steel hub/spider aluminum paddle blades.
- Pole adjusts center of fan from 43" to 60".
- Meets OSHA standards.
- 1 Year limited warranty.
- Imported to TPI specifications

### Motor Specifications

- 1-Phase
- 1/4 HP, 1/3 HP on HD Models
- Ball bearing
- Open ventilated
- 120V
- 2 or 3-Speed
- Permanently lubricated
- Permanent split capacitor

### Standard Models

MFG CATALOG NUMBER	MFG MODEL NUMBER	SIZE	HP	TYPE	MOUNT TYPE	CFM*			VELOCITY PROFILE	AMPS (HIGH)	WT. (LBS)
						HIGH	MED	LOW	CFM / Area Sq Ft		
08706202	CACU 24-P	24"	1/4	Standard	Pedestal Mount	3400	3100	2800	5400 / 220	2.3	63
08706402	CACU 24-W				Wall Mount						43
08697402	CACU 30-P	30"			Pedestal Mount	4200	3800	3500	6700 / 240	2.4	66
08706302	CACU 30-W				Wall Mount						46
08761702	CACU 30-P-HD	30"	1/3	Heavy Duty	Pedestal Mount	5000	4600	4200	7000 / 250	3.60	56

\*Measured 2 feet from face of fan

Note: Stocked models may differ in appearance from photograph

# TPI Commercial Oscillating Fans

Commercial wall mount and pedestal fans now available from TPI.

Units imported to TPI specifications.

### Standard Models



MFG CATALOG NUMBER	MFG MODEL NUMBER	SIZE	HP	TYPE	MOUNT TYPE	CFM*			VELOCITY PROFILE	AMPS			WT. (LBS)
						HIGH	MED	LOW	CFM / Area Sq Ft	HIGH	MED	LOW	
08748902	CACU 24-PO	24"	1/4	Standard	Pedestal Mount	3200	3000	2800	5100 / 230	1.45	1.15	1.1	68
08749102	CACU 24-WO				Wall Mount								48
08749002	CACU 30-PO	30"			Pedestal Mount	4200	3800	3500	6700 / 250	2.0	1.8	1.6	70
08749202	CACU 30-WO				Wall Mount								51
08761802	CACU 30-PO-HD	30"	1/3	Heavy Duty	Pedestal Mount	5000	4600	4200	7000 / 250	3.60	3.02	2.94	64

\*Measured 2 feet from face of fan

Note: Stocked models may differ in appearance from photograph - sizes are nominal.