



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CAR2S20DTRWH Vive 20A Recp DPLX TR

Lutron

Catalog Number	CAR2S20DTRWH
Manufacturer	Lutron
Description	Vive Wireless Receptacle, 20 A Duplex, In White
Weight per unit	0.3300 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
Number of Wires	3,4,5
Poles	2
Voltage Rating	120
Wattage	1500
Wire Size	12 to 14

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

Descriptions

Description	VIVE 20A RECP DPLX TR
extra long description	LUT CAR2S-20-DTR-WH 20A DUPLEX RF R
Features	The Wireless Receptacle is a radio-frequency (RF) receptacle switching solution that is capable of controlling 15 A or 20 A split or duplex style receptacles when paired with Pico wireless controls and Radio Powr Savr occupancy/vacancy sensors.
Long Description	Vive wireless receptacle, 20 A duplex, in white
Product Type	20A Duplex RF Receptacle White
Special Features	Dual switching. Utilizes Clear connect RF technology to communicate wirelessly to Pico wireless controls and Radio powr Savr occupancy/vacancy sensors. Capable of switching general purpose loads and downstream receptacles. 434 MHz



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276221948
Manufacturers Part Number	CAR2S-20-DTR-WH
UPC	784276221948

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Wireless duplex receptacle

Packaging

Carton	1
Weight Per each	0.33

Uses, Certifications, and Standards

environmental conditions	0 to 90% humidity, non-condensing
Mounting	WALLBOX
standard	cULus, FCC NOM, IFT
Temperature Rating	32 to 122