

Eaton CCP1044CD

Catalog Number: CCP1044CD

Eaton Crouse-Hinds series PowerMate CCP plug, 100A, 0.875-1.906", Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

Photo is representative

General specifications

| Product Name | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series PowerMate CCP plug | CCP1044CD |
| | UPC |
| | 662276276666 |
| Product Length/Depth | Product Height |
| 10.8 in | 4.13 in |
| Product Width | Product Weight |
| 4.13 in | 2.2 lb |



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

100A

Grounding type

Style 1

Configuration

Four-wire, four-pole

Cable diameter

0.875-1.906"

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CCP1044CD 3D drawing](#)

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

Installation instructions

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

Specifications and datasheets

[Eaton Specification Sheet - CCP1044CD](#)

[PowerMate Connectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)