

Eaton CCP20034CD

Catalog Number: CCP20034CD

Eaton Crouse-Hinds series PowerMate CCP plug, 200A, 0.875-1.906", Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications



| Product Name | Catalog Number |
|--|---------------------|
| Eaton Crouse-Hinds series PowerMate CCP plug | CCP20034CD |
| | UPC 662276364837 |
| Product Length/Depth | Product Height |
| 13.13 in | 7.5 in |
| Product Width | Product Weight |
| 7.5 in | 12.5 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

200A

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

0.875-1.906"

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CCP20034CD 3D drawing](#)

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

Installation instructions

[IF 1652 - 200A PowerMate Pin and Sleeve Devices](#)

Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CCP20034CD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)