

Specifications



Eaton CCP3023BC

Eaton Crouse-Hinds series PowerMate CCP plug, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CCP plug
CATALOG NUMBER	CCP3023BC
UPC	662276276536
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	2.31 in
PRODUCT WIDTH	2.31 in
PRODUCT WEIGHT	2.2 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds CCP3023BC 3D drawing
BROCHURES	PowerMate Drilling Pin and Sleeve Devices brochure
CATALOGS	PowerMate Drilling Pin and Sleeve Devices catalog page
CERTIFICATION REPORTS	PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors) PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors)
INSTALLATION INSTRUCTIONS	IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices
SPECIFICATIONS AND DATASHEETS	PowerMate Connectors Eaton Specification Sheet - CCP3023BC

Product specifications

AMPERAGE RATING	30A
GROUNDING TYPE	Style 2
CONFIGURATION	Two-wire, three-pole
CABLE DIAMETER	0.390-1.375"
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

