

Specifications

Photo is representative

Eaton CCP6023BC

Eaton Crouse-Hinds series PowerMate CCP plug, 60A, 0.440-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

Certifications and compliances

AREA CLASSIFICATION	Ordinary, Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CCP plug
CATALOG NUMBER	CCP6023BC
UPC	662276276635
PRODUCT LENGTH/DEPTH	8.17 in
PRODUCT HEIGHT	3.63 in
PRODUCT WIDTH	3.63 in
PRODUCT WEIGHT	2.2 lb



Powering Business Worldwide

Specifications

Photo is representative

Eaton CCP6023BC

Eaton Crouse-Hinds series PowerMate CCP plug, 60A, 0.440-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

Certifications and compliances

AREA CLASSIFICATION	Ordinary, Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CCP plug
CATALOG NUMBER	CCP6023BC
UPC	662276276635
PRODUCT LENGTH/DEPTH	8.17 in
PRODUCT HEIGHT	3.63 in
PRODUCT WIDTH	3.63 in
PRODUCT WEIGHT	2.2 lb



Powering Business Worldwide