

Eaton CCP6033BC

Catalog Number: CCP6033BC

Eaton Crouse-Hinds series PowerMate CCP plug, 60A, 0.440-1.375", Three-wire, three-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CCP plug	CCP6033BC
	UPC
	662276276628
Product Length/Depth	Product Height
8.17 in	3.63 in
Product Width	Product Weight
3.63 in	2.2 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

60A

Grounding type

Style 1

Configuration

Three-wire, three-pole

Cable diameter

0.440-1.375"

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CCP6033BC 3D drawing](#)

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

Installation instructions

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

Specifications and datasheets

[Eaton Specification Sheet - CCP6033BC](#)

[PowerMate Connectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)