

Eaton CDR3034 RS

Catalog Number: CDR3034 RS

Eaton Crouse-Hinds series PowerMate CDR receptacle, 30A, Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CDR receptacle	CDR3034 RS
	UPC
	662276277212
Product Length/Depth	Product Height
2.88 in	3.38 in
Product Width	Product Weight
3.38 in	2.2 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

30A

Grounding type

Style 2

Configuration

Three-wire, four-pole

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Special features

Reverse service

Resources

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CDR3034 RS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CDR3034 RS

Catalog Number: CDR3034 RS

Eaton Crouse-Hinds series PowerMate CDR receptacle, 30A, Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CDR receptacle	CDR3034 RS
	UPC
	662276277212
Product Length/Depth	Product Height
2.88 in	3.38 in
Product Width	Product Weight
3.38 in	2.2 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

30A

Grounding type

Style 2

Configuration

Three-wire, four-pole

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Special features

Reverse service

Resources

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CDR3034 RS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)