



**Product Number:** 29452

**Order Abbreviation:** CF23EL/BR40/827/RP

**General Description:** 23W Compact Fluorescent flood with intergral 120V ballast medium screw base color temperature 2700K 82CRI

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	CF23ELBR40827RP 6/CS 1/SKU
Average Rated Life (hr)	8000
Base	Medium
Bulb	BR40
Color Rendering Index (CRI)	82
Color Temperature/CCT (K)	2700
Diameter (in)	2.299
Diameter (mm)	58.40
Family Brand Name	Dulux® EL
Industry Standards	CSA, FCC 47CFR PART18 CONSUMER, UL
Initial Lumens at 25C	1200
Mean Lumens at 25C	1160
Maximum Overall Length - MOL (in)	6.5
Maximum Overall Length - MOL (mm)	165
Nominal Voltage (V)	120.00
Nominal Wattage (W)	23.00
Outside Diameter (in)	4.69
Outside Diameter (mm)	119.1





**Product Number:** 29452

**Order Abbreviation:** CF23EL/BR40/827/RP

**General Description:** 23W Compact Fluorescent flood with intergral 120V ballast medium screw base color temperature 2700K 82CRI

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	CF23ELBR40827RP 6/CS 1/SKU
Average Rated Life (hr)	8000
Base	Medium
Bulb	BR40
Color Rendering Index (CRI)	82
Color Temperature/CCT (K)	2700
Diameter (in)	2.299
Diameter (mm)	58.40
Family Brand Name	Dulux® EL
Industry Standards	CSA, FCC 47CFR PART18 CONSUMER, UL
Initial Lumens at 25C	1200
Mean Lumens at 25C	1160
Maximum Overall Length - MOL (in)	6.5
Maximum Overall Length - MOL (mm)	165
Nominal Voltage (V)	120.00
Nominal Wattage (W)	23.00
Outside Diameter (in)	4.69
Outside Diameter (mm)	119.1

