



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CGB194SA 1/2" Alu Dia Male Cord Grip (.375-.500)

Crouse-Hinds

Catalog Number	CGB194SA
Manufacturer	Crouse-Hinds
Description	Cord Gland, Steel With Zinc Electroplate and Chromate Finish Coat (Body, Gland Nut);Neoprene (Bushing) Material, CGB Model, 0.375 to 0.5 In Cable/Cord Size, 1.31 In Length, 1.23 In Diameter, Straight Male Connection, 1/2 In Thread Size, -25 °C Operating Temperature, +40 °C Operating Temperature, 0.08 LB
Weight per unit	0.0800 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	2.0200 IN X 1.2300 IN X 1.2300 IN

Material, Color, and Finish

Finish	Zinc Electroplated With Chromate Coated
--------	---

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Description	1/2" ALU DIA MALE CORD GRIP (.375-.500)
extra long description	CRS-H CGB194 SA 1/2 NPT MALE AL COR
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274140056
UPC	782274140056

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Weight Per each	0.08

Uses, Certifications, and Standards

Enclosure	Class I Div 2
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 40 Deg C