

# Eaton CH12L200R

Catalog Number: CH12L200R

Eaton CH main lug loadcenters, Cover included, Main lug only, 200A, D, Copper, NEMA 3R, Metallic, Overhead, CH, 12, 12, Three-wire, Single-phase, 120/240 V, #4 AWG-300 kcmil



## General specifications

### Product Name

Eaton CH main lug loadcenter

### Catalog Number

CH12L200R

### UPC

782113097404

### Product Length/Depth

29.13 in

### Product Height

5.19 in

### Product Width

14.31 in

### Product Weight

29.8 lb

### Warranty

Limited lifetime

### Certifications

UL 50

UL 67

### Catalog Notes

Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb.

## Product specifications

### Special features

Cover included

### Type

Main lug only

### Amperage Rating

200 A

### Bus material

Copper

### Feed type

Overhead

### Main circuit breaker

CH

### Number of circuits

12

### Number of spaces

12

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#4 AWG-300 kcmil

### Box size

D

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Number of wires

3

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CH12L200R](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)