

# Eaton CH20L125C

Catalog Number: CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1



## General specifications

|                              |  |
|------------------------------|--|
| <b>Product Name</b>          | <b>Catalog Number</b>  |
| Eaton CH main lug loadcenter | CH20L125C  |
| <b>UPC</b>                   | <b>Product Length/Depth</b>  |
| 782113097572                 | 29.13 in   |
| <b>Product Height</b>        | <b>Product Width</b>   |
| 3.88 in                      | 14.31 in   |
| <b>Product Weight</b>        | <b>Warranty</b>  |
| 15 lb                        | Limited lifetime   |
| <b>Certifications</b>        | <b>Catalog Notes</b>   |
| UL 50<br>UL 67               | Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. |

## Product specifications

### Type

Main lug only

### Amperage Rating

125 A

### Bus material

Copper

### Cover

Ch8cf-combination, ch8cs-surface

### Feed type

Top/bottom

### Main circuit breaker

CH

### Number of circuits

20

### Number of spaces

20

### Phase

Single-phase

### Wire size

#6-2/0 AWG

### Box size

C

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH20L125C

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CH20L125C

Catalog Number: CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1



## General specifications

|                              |  |
|------------------------------|--|
| <b>Product Name</b>          | <b>Catalog Number</b>  |
| Eaton CH main lug loadcenter | CH20L125C  |
| <b>UPC</b>                   | <b>Product Length/Depth</b>  |
| 782113097572                 | 29.13 in   |
| <b>Product Height</b>        | <b>Product Width</b>   |
| 3.88 in                      | 14.31 in   |
| <b>Product Weight</b>        | <b>Warranty</b>  |
| 15 lb                        | Limited lifetime   |
| <b>Certifications</b>        | <b>Catalog Notes</b>   |
| UL 50<br>UL 67               | Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. |

## Product specifications

### Type

Main lug only

### Amperage Rating

125 A

### Bus material

Copper

### Cover

Ch8cf-combination, ch8cs-surface

### Feed type

Top/bottom

### Main circuit breaker

CH

### Number of circuits

20

### Number of spaces

20

### Phase

Single-phase

### Wire size

#6-2/0 AWG

### Box size

C

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH20L125C

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)