

Specifications

Photo is representative



Eaton CH30L3150R

Eaton CH main lug loadcenter, Standard, Main lug only, 150 A, D, Copper, NEMA 3R, Metallic, Overhead, CH, 30 Circuits, 30 Spaces, Four-wire, Three-phase, #4 AWG-300 kcmil

Product specifications

SPECIAL FEATURES	Standard
TYPE	Main lug only
AMPERAGE RATING	150 A
BUS MATERIAL	Copper
FEED TYPE	Overhead
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	30
NUMBER OF SPACES	30
PHASE	Three-phase
WIRE SIZE	#4 AWG-300 kcmil
BOX SIZE	D
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	35 kAIC
NUMBER OF WIRES	4

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH30L3150R
UPC	782113097916
PRODUCT LENGTH/DEPTH	29.13 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	34.8 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Furnished with hub closure plates.

EATON

Powering Business Worldwide