

# Eaton CH32BPN200J

Catalog Number: CH32BPN200J

CH 3/4-inch loadcenter, Plug-on neutral, Main breaker, 200A, J, Copper, Ch8jf-combination, ch8js-surface, not included, NEMA 1, Metallic, 35 kAIC, CSH, 32, 32, Three-wire, Single-phase, #2/0 AWG-300 kcmil



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CH32BPN200J
<b>UPC</b>	<b>Product Length/Depth</b>
782116983377	34.13 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15.8 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Single phase convertible loadcenters with main breaker included

## Product specifications

### Special features

Plug-on neutral

### Type

Main breaker

### Amperage Rating

200 A

### Bus material

Copper

### Cover

Ch8jf-combination, ch8js-surface, not included

### Main circuit breaker

CSH

### Number of circuits

32

### Number of spaces

32

### Phase

Single-phase

### Wire size

#2/0 AWG-300 kcmil

### Box size

J

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

35 kAIC

### Number of wires

3

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CH32BPN200J](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)