

Specifications



Photo is representative

Eaton CH32N200R

Eaton CH 3/4-inch loadcenter, single-phase, 32 circuits, 32-pole, #2/0-300 kcmil wire, 200A, NEMA 3R

General specifications

PRODUCT NAME	Eaton CH convertible loadcenter
CATALOG NUMBER	CH32N200R
UPC	782113098531
PRODUCT LENGTH/DEPTH	34.13 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	35.5 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Furnished with hub closure plates.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Standard
TYPE	Convertible
AMPERAGE RATING	200 A
BUS MATERIAL	Copper
FEED TYPE	Overhead
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	32
NUMBER OF SPACES	32
PHASE	Single-phase
WIRE SIZE	#2/0 AWG-300 kcmil
BOX SIZE	J
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH32N200R
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

