

Specifications

Photo is representative

Eaton CH42B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil, Overhead, 120/240 V

Product specifications

SPECIAL FEATURES	Standard
TYPE	Main breaker
AMPERAGE RATING	200 A
BUS MATERIAL	Copper
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	42
NUMBER OF SPACES	42
PHASE	Single-phase
WIRE SIZE	#2 AWG-300 kcmil
FEED TYPE	Overhead
VOLTAGE RATING	120/240 V
BOX SIZE	K
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

General specifications

PRODUCT NAME	Eaton CH main breaker loadcenter
CATALOG NUMBER	CH42B200R
UPC	782113098227
PRODUCT LENGTH/DEPTH	37 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.5 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Furnished with hub closure plates. Loadcenter contains single insulated/bondable neutral.



Powering Business Worldwide

Specifications

Photo is representative

Eaton CH42B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil, Overhead, 120/240 V

Product specifications

SPECIAL FEATURES	Standard
TYPE	Main breaker
AMPERAGE RATING	200 A
BUS MATERIAL	Copper
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	42
NUMBER OF SPACES	42
PHASE	Single-phase
WIRE SIZE	#2 AWG-300 kcmil
FEED TYPE	Overhead
VOLTAGE RATING	120/240 V
BOX SIZE	K
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

General specifications

PRODUCT NAME	Eaton CH main breaker loadcenter
CATALOG NUMBER	CH42B200R
UPC	782113098227
PRODUCT LENGTH/DEPTH	37 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.5 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Furnished with hub closure plates. Loadcenter contains single insulated/bondable neutral.



Powering Business Worldwide