



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch main loadcenter

**CH60BPN225N**

**UPC:**786685425283

**Dimensions:**

- **Height:** 3.88 IN
- **Length:** 45 IN
- **Width:** 14.31 IN

**Notes:**225A max

**Warranties:**

- Limited lifetime

**Specifications:**

- **Special Features:** Plug-on neutral
- **Type:** Main breaker
- **Amperage Rating:** 225A
- **Box Size:** N
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 60
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Voltage Rating:** 120/240V, 208Y/120, or 240V

**Supporting documents:**

- [Eaton Specification Sheet - CH60BPN225N](#)

**Certifications:** No Data

**Product compliance:** No Data





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch main loadcenter

**CH60BPN225N**

**UPC:**786685425283

**Dimensions:**

- **Height:** 3.88 IN
- **Length:** 45 IN
- **Width:** 14.31 IN

**Notes:**225A max

**Warranties:**

- Limited lifetime

**Specifications:**

- **Special Features:** Plug-on neutral
- **Type:** Main breaker
- **Amperage Rating:** 225A
- **Box Size:** N
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 60
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Voltage Rating:** 120/240V, 208Y/120, or 240V

**Supporting documents:**

- [Eaton Specification Sheet - CH60BPN225N](#)

**Certifications:** No Data

**Product compliance:** No Data

