

Eaton CH60SPAST

Catalog Number: CH60SPAST

Eaton CH 3/4 in spa panel, ch spa panel-quick pro, single-phase, three-wire, 60 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature



General specifications

Product Name	Catalog Number
Eaton CH spa panel	CH60SPAST
UPC	Product Length/Depth
786685969909	9.5 in
Product Height	Product Width
3.13 in	1.5 in
Product Weight	Warranty
7.55 lb	Limited lifetime
Certifications	Catalog Notes
Contact Manufacturer	Includes a ch260gfi breaker, factory installed, and two extra circuits for convenience. Includes ground fault self-test feature.

Product specifications

Special features

Includes ch230gfi breaker GS ST

Type

Ch spa panel-quick pro

Amperage Rating

60A

Number Of Poles

Two-pole

Phase

Single-phase

Used with

Ch spa panel

Wire size

#14-1/0 AWG Cu/Al

Box size

5R

Enclosure

NEMA 3R

Number of wires

3

Size

3/4 in

Resources

Brochures

Specifications and datasheets

[Eaton Specification Sheet - CH60SPAST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)