



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH816GEN6060 8/16 Circuit Emergency PWR PNL/Manual Transfer Swi *Eaton Corp*

Catalog Number	CH816GEN6060
Manufacturer	Eaton Corp
Description	Eaton CH Transfer Switch Panel, Standard Manual Transfer Switch, For Square D QO48M60DSGP, 60A, 8 Spaces, 16 Circuits, Nema 1 Enclosure, 15 KW, Provisions For Feeder Breakers, to Opposite Phasing
Weight per unit	16.0 (lbs/each)
Product Category	Power Outlet Panel & Pedestal

Features

media	Yes
-------	-----

Dimensions and Weight

Depth	16.8
Height	14.3
Width	4.4

Descriptions

Description	8/16 CIRCUIT EMERGENCY PWR PNL/MANUAL TRANSFER SWI
extra long description	ETN CH816GEN6060 8/16 CKT EMER PWR
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH transfer switch panel, Standard manual transfer switch, For Square D QO48M60DSGP, 60A, 8 spaces, 16 circuits, NEMA 1 enclosure, 15 kW, Provisions for feeder breakers, TO opposite phasing
Product Type	8/16 CKT Emer PWR PNL/Man Trans Switch
Special Features	Used with Square D QO48M60DSGP

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114511800
Manufacturers Part Number	CH816GEN6060
UPC	782114511800

Taxonomies, Classifications, and Categories

Category Description	TRANSFER SWITCHES
Type	Transfer switch panel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	16

Uses, Certifications, and Standards

Application	Other
standard	UL 1008,UL 67