

# Specifications



## Eaton CHEC32N225KRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 32 Circuits

### Product specifications

<b>SPECIAL FEATURES</b>	Includes renovation terminal blocks
<b>TYPE</b>	Surge loadcenter
<b>AMPERAGE RATING</b>	225 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	32
<b>NUMBER OF SPACES</b>	32
<b>PHASE</b>	Single phase
<b>ENCLOSURE</b>	NEMA 3R
<b>INTERRUPT RATING</b>	25 kA

### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC32N225KRNSP
<b>UPC</b>	782116984183
<b>PRODUCT LENGTH/DEPTH</b>	37.5 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	22 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8KS or CHSUR8KF separately



Powering Business Worldwide

# Specifications



## Eaton CHEC32N225KRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 32 Circuits

### Product specifications

<b>SPECIAL FEATURES</b>	Includes renovation terminal blocks
<b>TYPE</b>	Surge loadcenter
<b>AMPERAGE RATING</b>	225 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	32
<b>NUMBER OF SPACES</b>	32
<b>PHASE</b>	Single phase
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kA

### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC32N225KRNSP
<b>UPC</b>	782116984183
<b>PRODUCT LENGTH/DEPTH</b>	37.5 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	22 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8KS or CHSUR8KF separately



Powering Business Worldwide