

Specifications



Eaton CHM1G7N7NS

Eaton pedestal mount metered, Metered-ring, Ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHM1G7N7NS
UPC	782114215586
PRODUCT LENGTH/DEPTH	31 in
PRODUCT HEIGHT	7.8 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231

Product specifications	
TYPE	Metered-ring
UTILITY APPROVALS	AZ : Salt River Project (SRP)
CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA 5-20R2GFI
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

Resources	
CATALOGS	Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHM1G7N7NS

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

