



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHNSURGE Type CH 2 Pole Surge Arrester

*Eaton Corp*

Catalog Number	CHNSURGE
Manufacturer	Eaton Corp
Description	Eaton Type CH Circuit Breaker Surge Protective Device, Two Pole, Surge Protective Device
Weight per unit	1.0 (lbs/each)
Product Category	Distribution Equipment

### Features

dimensions	3.5000 IN X 6.1000 IN X 2.4000 IN
------------	-----------------------------------

### Dimensions and Weight

Depth	3.5
Height	2.4
Width	6.1

### Descriptions

Description	TYPE CH 2 POLE SURGE ARRESTER
extra long description	ETN CHNSURGE Type CH 2 pole Surge A
Features	Eaton offers a comprehensive family of surge products for use at service entrances. These products can help protect sensitive electronics against the damaging effects of surges. Due to the evolution of electronics and microprocessors in the home, there is a continuous challenge to provide quality (clean) power for electronic loads such as appliances, computers/home office and entertainment systems. Surges caused by lightning, utility grid switching and other sources travel on current carrying conductors t
Long Description	Eaton Type CH circuit breaker surge protective device,Two Pole, Surge Protective Device
Product Type	Type CH 2 Pole Surge Arrester

### Manufacturer Information

Brand	Eaton
GTIN	00786689353650
Manufacturers Part Number	CHNSURGE
UPC	786689353650

### Taxonomies, Classifications, and Categories

Category Description	Meter Socket Accessories
Type	Plug on module surge protection device

### Packaging

Carton	1
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Other Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

standard

UL 1449,cUL Certified