

Specifications



Photo is representative



Eaton CHP24L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 48, 24, Three-wire, Single-phase

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CHP24L150R
UPC	786689058623
PRODUCT LENGTH/DEPTH	29 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES Cover included

TYPE Main Lug Only

AMPERAGE RATING 150 A

BUS MATERIAL Copper

FEED TYPE Overhead

NUMBER OF CIRCUITS 48

NUMBER OF SPACES 24

PHASE Single-phase

BOX SIZE X5

ENCLOSURE NEMA 3R

ENCLOSURE MATERIAL Metallic

INTERRUPT RATING 25 kAIC

NUMBER OF WIRES 3

Resources

MULTIMEDIA [AFCI Educational Video](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - CHP24L150R](#)

WARRANTY GUIDES [Eaton type CH circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

