



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHP24L225R CH Pon Loadcntr 225A Mlo 24 Space N3R *Eaton Corp*

Catalog Number	CHP24L225R
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenters, Cover Included, Main Lug Only, 225A, X5, Copper, Nema 3R, Metallic, Overhead, 48, 24, Three-Wire, Single-Phase
Weight per unit	27.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	225
interrupt rating	25
media	Yes
number of spaces	24
Phase	1

Dimensions and Weight

Depth	29
Height	5.19
Size	X5
Width	14.31

Descriptions

Description	CH PON LOADCNTR 225A MLO 24 SPACE N3R
extra long description	ETN CHP24L225R CH PON LC, 225A, MLO
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenters,Cover included,Main Lug Only,225A,X5,Copper,NEMA 3R,Metallic,Overhead,48,24,Three-wire,Single-phase
Product Type	CH Pon LC, 225A, Mlo, 24SP, N3R
Special Features	Cover included

Manufacturer Information

Brand	Eaton
GTIN	00786689058630
Manufacturers Part Number	CHP24L225R
UPC	786689058630



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LOADCENTERS & COVERS

Type Main lug loadcenter

Packaging

Carton 1

Weight Per each 27

Uses, Certifications, and Standards

Application Residential Bldgs & Facilities - Residential Bldgs & Facilities -
Other

standard UL 67,UL 50