

Specifications



Photo is representative



Eaton CHR8N8NSU

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: None, Ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR8N8NSU
UPC	786685404202
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	31 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	30 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL 231 UL Listed file E163588

Product specifications

SPECIAL FEATURES	Water resistant left/center receptacle
TYPE	Metered-ringless
CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	None
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 5-20R2GFI
RECEPTACLE RIGHT	None
FEED TYPE	Bottom
MOUNTING	Surface
NUMBER OF CIRCUITS	4

Resources

CATALOGS

[Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHR8N8NSU](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton CHR8N8NSU

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: None, Ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR8N8NSU
UPC	786685404202
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	31 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	30 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL 231 UL Listed file E163588

Product specifications

SPECIAL FEATURES	Water resistant left/center receptacle
TYPE	Metered-ringless
CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	None
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 5-20R2GFI
RECEPTACLE RIGHT	None
FEED TYPE	Bottom
MOUNTING	Surface
NUMBER OF CIRCUITS	4

Resources

CATALOGS

[Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHR8N8NSU](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

