

Eaton CHU7N7N5GS

Catalog Number: CHU7N7N5GS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Non-ground fault, Non-ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 5-20R2GFI, NEMA 6-20R2, 3, 3, 3, 125V, 125V, 250V

General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU7N7N5GS
UPC	Product Length/Depth
782114215753	4.3 in
Product Height	Product Width
17.1 in	9.5 in
Product Weight	Warranty
26 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.



Certifications

UL Listed file E163588
UL 231

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Ground fault

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 5-20R2GFI

Receptacle right

NEMA 6-20R2

Type

Unmetered

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHU7N7N5GS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia