



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHU9N9NS Pop Ringless 2 5-20R2GFI Receptacles Surface

Eaton Corp

Catalog Number	CHU9N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Water and Tamper Resistant Left/Center Receptacle, Unmetered, 20A, 20A, None, Non-GF, Non-Ground Fault, None, Top, Surface, Circuits: 4, Nema 5-20R2GFI(3), Nema 5-20R2GFI(3), None, 3, 3, 0, 125V, 125V, None
Weight per unit	15.0 (lbs/each)
Product Category	20191018094527

Features

Mounting Type	Surface
---------------	---------

Dimensions and Weight

Height	17.1
Length	4.3
Width	9.5

Descriptions

Description	POP RINGLESS 2 5-20R2GFI RECEPTACLES SURFACE
extra long description	ETN CHU9N9NS POP,RINGLESS,(2) 5-20R
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Water and tamper resistant left/center receptacle, Unmetered, 20A, 20A, None, Non-GF, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA 5-20R2GFI(3), NEMA 5-20R2GFI(3), None, 3, 3, 0, 125V, 125V, None
Product Type	Pop, Ringless, (2) 5-20R2GFI Recept, Surf
Special Features	Water and tamper resistant left/center receptacle

Manufacturer Information

Brand	Eaton Corp
GTIN	00786685404233
Manufacturers Part Number	CHU9N9NS
UPC	786685404233

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	15

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL 231,UL Listed file E163588