



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CL150 Type CL BRKR 50A/1POLE 120/240V 10K-Classified 1"

Eaton Corp

Catalog Number	CL150
Manufacturer	Eaton Corp
Description	Eaton Classified 3/4" Thermal Magnetic Circuit Breaker, Type CL 1-Inch Classified Replacement Breaker, 50 A, 10 Kaic, Single-Pole, 120/240V, CL, #14-4 Awg Cu/Al, CL, Type CH Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

amps	50
dimensions	3.0000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10
pole	Single
Poles	Single-pole
Voltage Rating	120/240 V

Descriptions

Description	TYPE CL BRKR 50A/1POLE 120/240V 10K-CLASSIFIED 1"
extra long description	ETN CL150 CL bkr 50A/1Pole 120/240V
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	Eaton Classified 3/4" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 50 A, 10 kAIC, Single-pole, 120/240V, CL, #14-4 AWG Cu/Al, CL, Type CH Loadcenters
Product Type	CL BKR 50A/1POLE 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676011617
Manufacturers Part Number	CL150
UPC	786676011617

Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	3/4" Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.3

Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489