



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville  
72802-0000, AR Russellville  
Phone: 479-967-2303  
Fax: 479-967-2306



## CPR26 2" Rigid Coupling Threadless

*Crouse-Hinds*

|                  |   |
|------------------|---|
| Catalog Number   | CPR26   |
| Manufacturer     | Crouse-Hinds  |
| Description      | Threadless Coupling, 2 In Trade Size, CPR Model, Straight, 162 LB/100 |
| Weight per unit  | 1.9 (lbs/each)  |
| Product Category | Rigid Conduit Fittings - Steel  |

### Features

|            |                                   |
|------------|-----------------------------------|
| dimensions | 3.0600 IN X 3.3100 IN X 3.3100 IN |
| Material   | Malleable Iron                    |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 2" RIGID COUPLING THREADLESS  |
| extra long description | MIDWEST CPR26 2 RGD CMP CPL   |
| Features               | Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00784564122261 |
| UPC   | 784564122261   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR |
| Type                 | Compression coupling   |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 2    |
| Weight Per each | 1.85 |

### Uses, Certifications, and Standards

|          |              |
|----------|--------------|
| standard | UL 514B, CUL |
|----------|--------------|