

Eaton CRC1044CD

Catalog Number: CRC1044CD

Eaton Crouse-Hinds series PowerMate CRC connector, 100A, 0.875-1.906", Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CRC connector	CRC1044CD
	UPC
	662276276727
Product Length/Depth	Product Height
11.5 in	3.44 in
Product Width	Product Weight
3.44 in	2.2 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

100A

Grounding type

Style 1

Configuration

Four-wire, four-pole

Cable diameter

0.875-1.906"

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CRC1044CD 3D drawing](#)

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CRC1044CD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CRC1044CD

Catalog Number: CRC1044CD

Eaton Crouse-Hinds series PowerMate CRC connector, 100A, 0.875-1.906", Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CRC connector	CRC1044CD UPC 662276276727
Product Length/Depth	Product Height
11.5 in	3.44 in
Product Width	Product Weight
3.44 in	2.2 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

100A

Grounding type

Style 1

Configuration

Four-wire, four-pole

Cable diameter

0.875-1.906"

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CRC1044CD 3D drawing](#)

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CRC1044CD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)