



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS115I 15A 120/277VAC S Wire Comm SP SW Iv *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | CS115I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Commercial 1-Pole Switch, Side-Wire, 15A 120/277V. |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| action | Single pole |
| amperage rating | 15 |
| Contact Rating | 15amp, 120/277vac |
| insulation | False |
| media | Yes |
| Poles | Single Pole |
| Switch Type | Toggle |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| extra long description | P&S CS15AC1I 15A 120/277VAC S WIRE |
| Long Description | Commercial 1-Pole Switch, Side-Wire, 15A 120/277V. |
| Product Type | 15A 120/277VAC S Wire Comm SP SW I |
| Special Features | Side wire, locking support, heavy duty toggle |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007126419 |
| Manufacturers Part Number | CS15AC1I |
| UPC | 785007126419 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | TOGGLE SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.15 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---------------------------|
| Application | Commercial |
| Enclosure | Nylon |
| Mounting | WALL |
| standard | CULUS, FEDSPEC, UL 498/20 |