



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CS320W 20A 120/277VAC S Wire Comm 3W SW WH *Pass & Seymour/LeGrand*

|                  |   |
|------------------|---|
| Catalog Number   | CS320W  |
| Manufacturer     | Pass & Seymour/LeGrand  |
| Description      | Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These Switches Offer Excellent Value While Meeting Federal Specification Standards. External Screw-Pressure-Plate Back Wiring Enables Fast Installation and Superior Electrical Connections. Rugged Construction Shrugs Off Hard Use and Abuse. |
| Weight per unit  | 0.1500 (lbs/each)   |
| Product Category | Gen Purpose Switches  |

### Features

|                       |  |
|-----------------------|--|
| action                | Three pole                                 |
| amperage rating       | 20   |
| connection            | Side Wire or external screw-pressure plate |
| Connection Type       | Wired                                      |
| Contact Configuration | One piece brass alloy contact arm          |
| Contact Rating        | Oversized silver alloy contacts            |
| Degree of Protection  | 1500V Dielectric Withstand Voltage         |
| indoor/outdoor        | Indoor                                     |
| insulation            | False                                      |
| Material              | Thermoplastic                              |
| media                 | Yes  |
| Poles                 | 3-way                                      |
| Switch Type           | Toggle                                     |
| Voltage               | 120/277 V                                  |
| Voltage Rating        | 120/277                                    |
| Wire Size             | #14 - #10 Awg                              |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### Dimensions and Weight

|      |        |
|------|--------|
| Size | 3.3 in |
|------|--------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| extra long description | P&S CS20AC3W 20A 120/277VAC S WIRE  |
| Long Description       | Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse. |
| Product Type           | 20A 120/277VAC S Wire Comm 3W SW W  |
| Special Features       | Back & Side wire, locking support, one piece brass alloy contact arm  |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007126556         |
| Manufacturers Part Number | CS20AC3W               |
| UPC                       | 785007126556           |

## Taxonomies, Classifications, and Categories

|                      |                     |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type                 | SWITCH              |

## Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 0.15 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Commercial   |
| Enclosure   | Nylon  |
| Mounting    | WALL   |
| nema rating | WD-1 and WD-6  |
| standard    | CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC |